

AQ-2000 Features & Options

Washers and Sanitizers to Automatically Wash and Apply Disinfectant to Wheelchairs and Other Hard-to-Clean Medical Equipment.

WHEEL ROTATION SYSTEM STANDARD

Includes Oscillating Spray Arms & Wheelchair Wheel Rotation System

STANDARD FEATURES

Structural

- Double Wall Stainless Steel Chamber
- Stainless Steel Structural Frame
- Stainless Steel Control Enclosure
- Oscillating Stainless Steel Spray Arms
- Caster Wheels (2,400lb rating)
- Seal Welded Wash Chamber
- Front Door 12ga Stainless Steel
- Wheelchair Wheel Rotation System

Controls & Electrical

- Programmable Logic Control Syst (PLC)
- 24 Volt DC Control System
- LCD Status Display
- Level Control Self Diagnostics
- Power Cord with GFCI Built in Circuit
- 115 Volt. 20 Amp. 60 Hertz System
- UL, CSA, CE/EU

Cycles

- Variable Time Cycles (3, 5, or 7 min)
- Run Mode & Drain Mode Selection
- Clean & Rinse Wash Cycles
- Automatic Chemical Injection
- Automatic Filling & Draining

Mechanical

- 1 HP Motor / Stainless Steel Pump
- Wheelchair Loading Carriage Assm

Wash System Nozzle Data

- Wash & Rinse System Nozzles: 23
- Wash PSI: 22
- Capacity Gallons/min: 37.5
- Capacity Gallons/cycle: 262.5
- Capacity Gallons/hour: 2250

• Fill & Drain Hose Set - 10' Each



OPTIONAL FEATURES & UPGRADES

- Disinfectant Application System
- Front Door Safety Window
- Lighted Wash Chamber
- Utility Wash Tray Set Stainless Steel
- Equipment Wash Rack SS HME/DME
- Digital Temperature Display
- Non-Reset Cycle Counter
- Wash Cycle Pressure Monitoring
- Loading Ramps
- Disinfectant Application Spray Wand (Exterior Mounted)

- Wash-Down Spray Gun & Hose (Exterior Mounted)
- Back Flow Prevention Devices / Systems
- Water Supply Temperature Mixing Valve (1/2" or 3/4" Line Size)
- Disinfectant Mixing Station (Exterior Mounted)
- Fill Line Water Temperature Gauge 3" Dial
- 1-1/2HP Motor / Stainless Steel Pump
- 208/230v, 25Amp, 50/60Hz, Single Phase Operation
- Specialized Cycle Sequencing
- Air Dry Blower

DIMENSIONS & WEIGHT -

Exterior

- Length: 68-1/16"
 Length: 50-1/4"
- Width: 34"
- Height: 61-5/8"

Chamber w/ Wheel Rotation System

- Width: 25-3/4"
- Height: 34-3/4"

Crate/Pallet Dimensions Approximate Shipping

- Length: 71"
- Width: 39"
- Height: 74"

Weight

- 950 lbs.
- 431 Kilo

Once the Aqua Phase unit is in its location, all you need to do is hook up two hoses - one for the hot water fill line and one for the drain line. Then plug the Aqua Phase in an appropriate power source & begin saving time, improving efficiency & enhancing your infection control protocol.